# High Reliability Power Inductors MS433PYA



- High temperature materials allow operation in ambient temperatures up to 155°C
- Tin-lead (Sn-Pb) termination for the best possible board adhesion
- Exceptionally low DCR 5.81 mOhm
- Soft saturation makes them ideal for VRM/VRD applications.

**Terminations** Tin-lead (63/37) over copper. **Core material** Composite

**Weight** 0.17 – 0.18 g

Ambient temperature -55°C to +105°C with Irms current

Maximum part temperature +155°C (ambient + temp rise) Storage temperature Component: -55°C to +155°C.

Tape and reel packaging: -55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Enhanced crush-resistant packaging 1000/7" reel Plastic tape: 12 mm wide, 0.23 mm thick, 8 mm pocket spacing, 2.3 mm pocket depth

Part number <sup>1</sup>	Inductance <sup>2</sup> ±20% (μH)	DCR (mOhms) <sup>3</sup>		SRF (MHz) <sup>4</sup>		Isat⁵	Irms (A) <sup>6</sup>	
		typ	max	min	typ	(A)	20°C rise	40°C rise
MS433PYA221MSZ	0.22	5.81	6.40	153	191	18.7	9.0	12.6
MS433PYA401MSZ	0.4	7.55	8.30	116	145	12.5	7.5	10.5
MS433PYA601MSZ	0.6	9.50	10.45	85	106	10.4	5.9	8.7
MS433PYA102MSZ	1.0	13.25	14.60	63	79	8.7	5.0	7.2
MS433PYA152MSZ	1.5	21.45	23.60	51	64	7.1	3.9	5.6
MS433PYA222MSZ	2.2	35.20	38.70	42	52	5.6	3.0	4.1

1. When ordering, please specify screening code:

### MS433PYA222MSZ

- Screening: Z = Unscreened
  - Y = Unscreened (SLDC Option A)
  - W = Unscreened (SLDC Option B)
  - H = Group A screening per Coilcraft CP-SA-10001
  - **G** = Coilcraft CP-SA-10001 Group A (SLDC Option A)
  - $\mathbf{D}$  = Coilcraft CP-SA-10001 Group A (SLDC Option B)

All screening performed to the document's latest revision

- 2. Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc.
- 3. DCR measured on a micro-ohmmeter.
- 4. SRF measured using an Agilent/HP 4395A or equivalent.
- 5. DC current at 25°C that causes an inductance drop of 30% (typ) from its value without current.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
- 7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

### **Irms Testing**

Irms testing was performed on a 0.060" inch thick pcb with 4 oz copper traces optimized to minimize additional termperature rise.


Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.



CRITICAL PRODUCTS & SERVICES © Coilcraft, Inc. 2023 Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com

#### Document MS806-1 Revised 05/02/23

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.



## **MS433PYA High Reliability Power Inductors**



© Coilcraft, Inc. 2023

1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363 Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com Document MS806-2 Revised 05/02/23


This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.


## **MS433PYA High Reliability Power Inductors**





Equivalent Series Resistance (Ohms)

### L vs Frequency









\*Height dimension shown is for the mounted part after reflow. Dimension before mounting can be an additional 0.008 inch / 0,2 mm.

Dimensions are in  $\frac{inches}{mm}$ 



© Coilcraft, Inc. 2023

1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363 Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com

#### Document MS806-3 Revised 05/02/23

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.