


Outgassing Compliant Power Inductors AR425PJB



- High temperature materials allow operation in ambient temperatures up to 155°C
- Passes NASA low outgassing specifications
- Special construction allows it to pass vibration testing to 80 G and shock testing to 1000 G.
- Tin-lead (Sn-Pb) termination for the best possible board adhesion
- Non-metallic cover suitable for space applications

Core material Ferrite

Terminations Tin-lead (63/37) over tin over nickel.

Weight 95 – 120 mg

Ambient temperature –55°C to +105°C with Irms current

Maximum part temperature +155°C (ambient + temp rise)

Storage temperature Component: –55°C to +155°C.

Packaging: –55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles


Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Enhanced crush-resistant packaging 1000/7" reel


Plastic tape: 12 mm wide, 0.23 mm thick, 8 mm pocket spacing, 1.9 mm pocket depth

Recommended pick and place nozzle OD: 4 mm; ID: ≤ 2 mm

Typical L vs Frequency



Typical L vs Current



AR425PJB Series (4018)

Part number ¹	Inductance ² (μ H)	DCR max ³ (Ohms)	SRF (MHz) ⁴		Isat (A) ⁵			Irms (A) ⁶	
			min	typ	10% drop	20% drop	30% drop	20°C rise	40°C rise
AR425PJB351MSZ	0.35 \pm 20%	0.040	252	360	5.9	6.1	6.3	2.2	3.1
AR425PJB561MSZ	0.56 \pm 20%	0.030	175	250	4.8	5.2	5.3	1.9	2.8
AR425PJB102NSZ	1.0 \pm 30%	0.040	126	180	2.8	3.0	3.1	1.8	2.7
AR425PJB222MSZ	2.2 \pm 20%	0.070	63	90	2.7	2.8	2.9	1.6	2.3
AR425PJB262MSZ	2.6 \pm 20%	0.080	59	85	2.6	2.7	2.8	1.5	2.0
AR425PJB332MSZ	3.3 \pm 20%	0.080	52	75	2.1	2.3	2.4	1.4	2.0
AR425PJB472MSZ	4.7 \pm 20%	0.125	45	65	1.8	1.9	1.9	1.3	1.8
AR425PJB682MSZ	6.8 \pm 20%	0.150	35	50	1.2	1.3	1.3	1.0	1.5
AR425PJB103MSZ	10 \pm 20%	0.200	28	40	1.1	1.2	1.3	0.90	1.25
AR425PJB153MSZ	15 \pm 20%	0.260	22	32	0.86	0.91	0.94	0.80	1.12
AR425PJB183MSZ	18 \pm 20%	0.270	18	27	0.78	0.83	0.85	0.70	1.00
AR425PJB223MSZ	22 \pm 20%	0.360	18	26	0.74	0.80	0.83	0.65	0.90
AR425PJB333MSZ	33 \pm 20%	0.420	14	20	0.58	0.64	0.68	0.55	0.80
AR425PJB473MSZ	47 \pm 20%	0.650	11	16	0.51	0.55	0.56	0.45	0.68
AR425PJB683MSZ	68 \pm 20%	0.950	9.0	13	0.41	0.45	0.46	0.40	0.56
AR425PJB104MSZ	100 \pm 20%	1.40	7.0	10	0.34	0.36	0.37	0.35	0.50
AR425PJB124MSZ	120 \pm 20%	1.60	6.0	9.0	0.31	0.33	0.34	0.30	0.45
AR425PJB154MSZ	150 \pm 20%	2.00	5.6	8.0	0.27	0.29	0.30	0.28	0.40
AR425PJB184MSZ	180 \pm 20%	2.50	5.2	7.5	0.24	0.26	0.27	0.26	0.36
AR425PJB224MSZ	220 \pm 20%	3.70	4.5	6.5	0.21	0.225	0.235	0.20	0.30
AR425PJB334MSZ	330 \pm 20%	5.90	3.8	5.5	0.18	0.19	0.20	0.17	0.23
AR425PJB474MSZ	470 \pm 20%	7.80	3.0	4.5	0.14	0.16	0.17	0.15	0.20
AR425PJB564MSZ	560 \pm 20%	10.0	2.8	4.0	0.13	0.14	0.15	0.14	0.18
AR425PJB684MSZ	680 \pm 20%	11.5	2.4	3.5	0.12	0.13	0.14	0.12	0.16
AR425PJB824MSZ	820 \pm 20%	14.0	2.0	2.9	0.11	0.12	0.13	0.10	0.14
AR425PJB105MSZ	1000 \pm 20%	18.0	1.9	2.8	0.10	0.11	0.11	0.098	0.125
AR425PJB155MSZ	1500 \pm 20%	25.0	1.6	2.4	0.095	0.10	0.105	0.080	0.110
AR425PJB185MSZ	1800 \pm 20%	31.5	1.6	2.3	0.090	0.095	0.100	0.070	0.095
AR425PJB225MSZ	2200 \pm 20%	32.5	1.4	2.1	0.088	0.099	0.100	0.070	0.090
AR425PJB335MSZ	3300 \pm 20%	48.0	1.1	1.6	0.082	0.092	0.094	0.055	0.075


1. When ordering, please specify **screening** code:

AR425PJB335MSZ

Screening:

- Z = Unscreened
- H = Coilcraft CP-SA-10001 Group A
- G = Coilcraft CP-SA-10001 Group A (SLDC Option A)
- D = Coilcraft CP-SA-10001 Group A (SLDC Option B)
- 1 = EEE-INST-002 (Family 1) Level 1
- 2 = EEE-INST-002 (Family 1) Level 2
- 3 = EEE-INST-002 (Family 1) Level 3
- 4 = MIL-STD-981 (Family 04) Class B
- 5 = MIL-STD-981 (Family 04) Class S
- F = Screening per ESCC 3201
- Screening performed to the document's latest revision.
- Lot qualification (Group B) available.
- Testing T and U have been replaced with more detailed codes 4, 5, and 1, 2, 3, respectively. Codes T and U can still be used, if necessary. Custom testing also available.
- Country of origin restrictions available; prefix options G or F.

2. Inductance tested at 100 kHz, 0.1 Vrms using an Agilent/HP 4192A. Inductance at 1 MHz is the same for parts with SRF \geq 10 MHz.
 3. DCR measured on a micro-ohmmeter.
 4. SRF measured using Agilent/HP 8753ES or equivalent.
 5. DC current that causes the specified inductance drop from its value without current.
 6. Current that causes the specified temperature rise from 25°C ambient.
 7. Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



CRITICAL PRODUCTS & SERVICES

1102 Silver Lake Road
Cary, IL 60013
Phone 800-981-0363

Fax 847-639-1508
Email cps@coilcraft.com
www.coilcraft-cps.com

Document AR435-2 Revised 09/13/22

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.