

# High Reliability Power Inductors ST465PYA



- Exceptionally low DCR – 4.83 mOhm
- Soft saturation makes them ideal for VRM/VRD applications.

**Terminations** Tin-silver (96.5/3.5) over copper.

**Core material** Composite

**Weight** 0.33 – 0.42 g

**Ambient temperature** –40°C to +125°C with Irms current

**Maximum part temperature** +165°C (ambient + temp rise).

**Storage temperature** Component: –55°C to +165°C.

Tape and reel packaging: –55°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Enhanced crush-resistant packaging** 500/7" reel

Plastic tape: 12 mm wide, 0.3 mm thick, 8 mm pocket spacing, 4.27 mm pocket depth

Part number <sup>1</sup>	Inductance <sup>2</sup> ±20% (µH)	DCR (mOhms) <sup>3</sup>		SRF (MHz) <sup>4</sup>		Isat (A) <sup>5</sup>	Irms (A) <sup>6</sup>	
		typ	max	min	typ		20°C rise	40°C rise
ST465PYA521MLZ	0.52	4.83	5.31	104	130	13.1	10.0	12.0
ST465PYA681MLZ	0.68	5.74	6.31	80	100	11.6	9.2	11.3
ST465PYA821MLZ	0.82	6.65	7.32	76	95	11.0	8.1	10.2
ST465PYA102MLZ	1.0	7.54	8.29	62	78	10.3	7.8	10.2
ST465PYA152MLZ	1.5	10.3	11.3	55	69	9.4	6.1	8.5
ST465PYA222MLZ	2.2	15.2	16.7	43	54	7.4	4.9	6.8
ST465PYA332MLZ	3.3	26.5	29.2	33	41	5.4	3.7	5.1
ST465PYA472MLZ	4.7	33.7	37.1	26	33	4.9	3.0	4.3
ST465PYA682MLZ	6.8	44.9	49.4	24	30	4.8	2.7	3.5
ST465PYA822MLZ	8.2	60.8	66.9	21	27	4.0	2.3	3.0
ST465PYA103MLZ	10	84.0	92.4	19	24	3.0	2.0	2.7
ST465PYA153MLZ	15	109	120	16	20	2.8	1.7	2.3

1. When ordering, please specify **screening** code:

**ST465PYA153MLZ**

**Screening:** Z = Unscreened

Y = Unscreened (SLDC Option A)

W = Unscreened (SLDC Option B)

H = Group A screening per Coilcraft CP-SA-10001

G = Coilcraft CP-SA-10001 Group A (SLDC Option A)

D = Coilcraft CP-SA-10001 Group A (SLDC Option B)

All screening performed to the document's latest revision

2. Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc.

3. DCR measured on a micro-ohmmeter.

4. SRF measured using an Agilent/HP 4395A or equivalent.

5. DC current at 25°C that causes a 30% (typ) inductance drop from its value without current.

6. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.

7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.













## Irms Testing

Irms testing was performed on a 0.060" thick pcb with 4 oz. copper traces optimized to minimize additional temperature rise.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.

# ST465PYA Series

## L vs Current



CRITICAL PRODUCTS & SERVICES

1102 Silver Lake Road  
Cary, IL 60013  
Phone 800-981-0363


Fax 847-639-1508  
Email [cps@coilcraft.com](mailto:cps@coilcraft.com)  
[www.coilcraft-cps.com](http://www.coilcraft-cps.com)

Document ST803-2 Revised 08/08/23






This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

# ST465PYA Series

## L vs Frequency



## ESR vs Frequency



\* Height dimension shown is for the mounted part after reflow. Dimension before mounting can be an additional 0.005 inch / 0.13 mm.

Dimensions are in  $\frac{\text{inches}}{\text{mm}}$



CRITICAL PRODUCTS & SERVICES

1102 Silver Lake Road  
Cary, IL 60013  
Phone 800-981-0363

Fax 847-639-1508  
Email cps@coilcraft.com  
www.coilcraft-cps.com

Document ST803-3 Revised 08/08/23

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.