


High Reliability Power Inductors ML390PZA



- High temperature materials allow operation in ambient temperatures up to 155°C
- Low profile, ultra-miniature, shielded power inductor
- Soft saturation makes them ideal for VRM/VRD applications.

Terminations Tin-silver-copper over tin over nickel over silver.

Core material Composite

Weight 44 mg

Ambient temperature -55°C to +105°C with Irms current

Maximum part temperature +155°C (ambient + temp rise)

Storage temperature Component: -55°C to +155°C.

Tape and reel packaging: -55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Enhanced crush-resistant packaging 2000/7" reel

Plastic tape: 8 mm wide, 0.23 mm thick, 4 mm pocket spacing, 1.14 mm pocket depth

Part number ¹	Inductance ² ±20% (µH)	DCR (mOhms) ³		SRF (MHz) ⁴		Isat (A) ⁵			Irms (A) ⁶	
		typ	max	min	typ	10% drop	20% drop	30% drop	20°C rise	40°C rise
ML390PZA601MLZ	0.60	30	33	144	180	1.8	2.4	2.7	1.8	2.5
ML390PZA102MLZ	1.0	43	49	102	128	1.5	2.1	2.4	1.6	2.3
ML390PZA152MLZ	1.5	71	80	77	97	1.2	1.6	1.9	1.4	1.9
ML390PZA222MLZ	2.2	111	122	62	78	0.94	1.2	1.5	1.0	1.3
ML390PZA332MLZ	3.3	154	166	51	64	0.86	1.1	1.3	0.88	1.2
ML390PZA472MLZ	4.7	217	230	45	57	0.71	0.97	1.1	0.84	1.1


1. When ordering, please specify **screening** code:

ML390PZA472MLZ

Screening: Z = Unscreened
 Y = Unscreened (SLDC Option A)
 W = Unscreened (SLDC Option B)
 H = Group A screening per Coilcraft CP-SA-10001
 G = Coilcraft CP-SA-10001 Group A (SLDC Option A)
 D = Coilcraft CP-SA-10001 Group A (SLDC Option B)
 All screening performed to the document's latest revision

- Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc.
- DCR measured on a micro-ohmmeter.
- SRF measured using Agilent/HP 4395A or equivalent.
- DC current at 25°C that causes the specified inductance drop from its value without current.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
- Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Dimensions are in $\frac{\text{inches}}{\text{mm}}$

Coilcraft CPS
 CRITICAL PRODUCTS & SERVICES

1102 Silver Lake Road
 Cary, IL 60013
 Phone 800-981-0363







Fax 847-639-1508
 Email cps@coilcraft.com
 www.coilcraft-cps.com

Document ML727-1 Revised 05/23/23


This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

ML390PZA Series

L vs Current



L vs Frequency



CRITICAL PRODUCTS & SERVICES

1102 Silver Lake Road
Cary, IL 60013
Phone 800-981-0363

© Coilcraft, Inc. 2023

Fax 847-639-1508
Email cps@coilcraft.com
www.coilcraft-cps.com

Document ML727-2 Revised 05/23/23

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.