
Shielded Power Inductors AE624PYA



	Inductance ²	DCR (mOhms) ³		SRF (MHz) ⁴		Isat ⁵	Irms (A) ⁶	
Part number ¹	±20% (μΗ)	typ	max	typ	min	(A)	20°C rise	40°C rise
AE624PYA472MSZ	4.7	3.35	3.8	12.7	10.1	39.0	18.7	21.7
AE624PYA682MSZ	6.8	4.17	4.6	11.5	9.2	36.0	14.2	19.5
AE624PYA822MSZ	8.2	6.00	7.5	10.8	8.6	30.0	13.5	18.0
AE624PYA103MSZ	10	6.80	9.0	10.1	8.0	26.3	12.0	16.5
AE624PYA153MSZ	15	9.17	12.4	8.0	6.4	23.0	9.7	13.5
AE624PYA223MSZ	22	14.5	16.0	6.3	5.0	18.7	7.8	10.5
AE624PYA333MSZ	33	18.7	20.0	5.8	4.6	16.7	6.4	9.0

1. When ordering, please specify screening code:

AE624PYA333MSZ

- Screening: Z = Unscreened
 - H = Coilcraft CP-SA-10001 Group A
 - G = Coilcraft CP-SA-10001 Group A (SLDC Option A)
 - D = Coilcraft CP-SA-10001 Group A (SLDC Option B)
 - 1 = EEE-INST-002 (Family 1) Level 1
 - 2 = EEE-INST-002 (Family 1) Level 2
 - 3 = EEE-INST-002 (Family 1) Level 3
 - 4 = MIL-STD-981 (Family 04) Class B
 - 5 = MIL-STD-981 (Family 04) Class S
 - F = ESCC3201 (F4 operational life performed at 105°C)
 - · Screening performed to the document's latest revision.
 - Lot qualification (Group B) available.
 - Testing T and U have been replaced with more detailed codes 4, 5, and 1, 2, 3, respectively. Codes T and U can still be used, if necessary. Custom testing also available.
 - Country of origin restrictions available; prefix option G.
 - · SLDC is limited to 1000 pcs lots

- High temperature materials allow operation in ambient temperatures up to 155°C
- High current; very low DCR
- Passes NASA low outgassing specifications
- Soft saturation makes them ideal for VRM/VRD applications
- Passes vibration testing to 30 G and shock testing to 100 G
- Special coating ensures DWV compliance with MIL-STD-981 screening

Core material Composite

Terminations Tin-lead (63/37) over copper

Weight 12.4 - 15.5 a

Ambient temperature -55°C to +105°C with (40°C rise) Irms current. Maximum part temperature +155°C (ambient + temp rise). Derating. Storage temperature Component: -55°C to +155°C. Tape and reel packaging: -55°C to +80°C Resistance to soldering heat Max three 40 second reflows at

+260°C, parts cooled to room temperature between cycles Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787_PCB_Washing.pdf.

SRF (MHz) ⁴			Isat ⁵	Irms (A) ⁶		
typ min		min	(A)	20°C rise	40°C rise	
	12.7	10.1	39.0	18.7	21.7	
	11.5	9.2	36.0	14.2	19.5	
	10.8	8.6	30.0	13.5	18.0	
	10.1	8.0	26.3	12.0	16.5	
	8.0	6.4	23.0	9.7	13.5	
	6.3	5.0	18.7	7.8	10.5	
	5.8	4.6	16.7	6.4	9.0	

2. Inductance tested at 100 kHz. 0.1 Vrms. 0 Adc.

- 3. DCR measured on a micro-ohmmeter.
- 4. SRF measured using Agilent/HP 4395A or equivalent.
- 5. DC current at 25°C that causes an inductance drop of 30% (typ) from its value without current.
- 6. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
- 7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Irms Testing

Irms testing was performed on a 0.060" thick pcb with 4 oz. copper traces optimized to minimize additional temperature rise.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.




© Coilcraft, Inc. 2022

1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363

Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com

Document AE947-1 Revised 09/29/22

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.



Shielded Power Inductors – AE624PYA





© Coilcraft, Inc. 2022

1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363 Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com Document AE947-2 Revised 09/29/22

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

Shielded Power Inductors – AE624PYA





Packaging 150/13" reel Plastic tape: 32 mm wide, 0.3 mm thick, 24 mm pocket spacing, 10.26 mm pocket depth (**all except -333**) 11.26 mm pocket depth (**-333 only**).



© Coilcraft, Inc. 2022

1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363 Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com Document AE947-3 Revised 09/29/22

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.