# 200°C Air Core Inductors AT475RAT



- High Q over a wide range of frequencies
- Special materials allow operation in ambient temperatures as low as −60°C and up to 200°C.
- Passes NASA low outgassing specifications

Terminations Tin-lead (63/37) over copper

Weight 80 - 200 mg

Ambient temperature -60°C to +150°C with Imax current

Maximum part temperature +200°C (ambient + temp rise).

Storage temperature Component: -60°C to +200°C.

Tape and reel packaging: -55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Temperature Coefficient of Inductance (TCL) +5 to +70 ppm/°C Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

**Enhanced crush-resistant packaging** 500 per 7" reel Plastic tape: 12 mm wide, 0.3 mm thick, 8 mm pocket spacing, 4.2 mm pocket depth

Part number <sup>1</sup>	Inductance <sup>2</sup> (nH)	Percent tolerance	Q³ typ	Q³ min	SRF min⁴ (GHz)	DCR max <sup>5</sup> (mOhm)	Imax (A)
AT475RAT22N_SZ	22	5,2	135	100	3.2	4.2	3.0
AT475RAT27N_SZ	27	5,2	135	100	2.7	4.0	3.5
AT475RAT33N_SZ	33	5,2	130	100	2.5	4.8	3.0
AT475RAT39N_SZ	39	5,2	135	100	1.8	4.4	3.0
AT475RAT47N_SZ	47	5,2	135	100	2.1	5.6	3.0
AT475RAT56N_SZ	56	5,2	125	100	1.5	6.2	3.0
AT475RAT68N_SZ	68	5,2	120	100	1.5	8.2	2.5
AT475RAT82N_SZ	82	5,2	120	100	1.3	9.4	2.5
AT475RATR10_SZ	100	5,2	115	100	1.2	12.3	1.7
AT475RATR12_SZ	120	5,2	125	100	1.1	17.3	1.5
AT475RATR15_SZ	150	5,2	145	100	0.75	33.0	1.2

1. When ordering, specify tolerance and screening codes:

#### AT475RATR15GSZ

Tolerance: Screening: G = 2% J = 5%

Z = Unscreened

H = Coilcraft CP-SA-10001 Group A

**F** = ESCC3201 (F4 operational life performed at 90°C)

- 1 = EEE-INST-002 (Family 3) Level 1
- 2 = EEE-INST-002 (Family 3) Level 2
- 3 = EEE-INST-002 (Family 3) Level 3
- **4** = MIL-STD-981 (Family 50) Class B **5** = MIL-STD-981 (Family 50) Class S
- Screening performed to the document's latest revision.
- Screening not available for parts with 2% tolerance.
- Testing is performed using 155°C as max component temperature.
- Lot qualification (Group B) available.
- Testing T and U have been replaced with more detailed codes 4, 5, and 1, 2, 3, respectively. Codes T and U can still be used, if necessary. Custom testing also available.
- Country of origin restrictions available; prefix option G.

- Inductance measured at 150 MHz on an Agilent/HP 4286A or equivalent with a Coilcraft SMD-A test fixture and correlation.
- 3. Q measured at 150 MHz on an Agilent/HP 4291A or equivalent with a 16193A test fixture or equivalent.
- 4. SRF measured on an Agilent/HP 8753ES or equivalent with a Coilcraft CCF1268 test fixture.
- 5. DCR measured on a Keithley 580 Micro-Ohmmeter or equivalent.
- 6. Electrical specifications at 25°C.


Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Document AT184-1 Revised 12/06/22

# **AT475RAT Air Core Inductors**

## **Typical L vs Frequency**



## **Typical Q vs Frequency**

