


High Reliability Power Inductors ML433PYA



- High temperature materials allow operation in ambient temperatures up to 155°C
- Exceptionally low DCR – 5.81 mOhm
- Soft saturation makes them ideal for VRM/VRD applications.

Terminations Tin-silver over copper.

Core material Composite

Weight 0.17 – 0.18 g

Ambient temperature –55°C to +105°C with Irms current

Maximum part temperature +155°C (ambient + temp rise)

Storage temperature Component: –55°C to +155°C

Tape and reel packaging: –55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Enhanced crush-resistant packaging 1000/7" reel

Plastic tape: 12 mm wide, 0.23 mm thick, 8 mm pocket spacing, 2.3 mm pocket depth

Part number ¹	Inductance ² ±20% (µH)	DCR (mOhms) ³		SRF (MHz) ⁴		Isat ⁵ (A)	Irms (A) ⁶	
		typ	max	min	typ		20°C rise	40°C rise
ML433PYA221MLZ	0.22	5.81	6.40	153	191	18.7	9.0	12.6
ML433PYA401MLZ	0.40	7.55	8.30	116	145	12.5	7.5	10.5
ML433PYA601MLZ	0.60	9.50	10.45	85	106	10.4	5.9	8.7
ML433PYA102MLZ	1.0	13.25	14.60	63	79	8.7	5.0	7.2
ML433PYA152MLZ	1.5	21.45	23.60	51	64	7.1	3.9	5.6
ML433PYA222MLZ	2.2	35.20	38.70	42	52	5.6	3.0	4.1

1. When ordering, please specify **screening** code:

ML433PYA222MSZ

Screening: Z = Unscreened

H = Group A screening per Coilcraft CP-SA-10001

G = Coilcraft CP-SA-10001 Group A (SLDC Option A)

D = Coilcraft CP-SA-10001 Group A (SLDC Option B)

All screening performed to the document's latest revision

- Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc.
 - DCR measured on a micro-ohmmeter.
 - SRF measured using an Agilent/HP 4395A or equivalent.
 - DC current at 25°C that causes an inductance drop of 30% (typ) from its value without current.
 - Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
 - Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.







Irms Testing

Irms testing was performed on a 0.060" inch thick pcb with 4 oz copper traces optimized to minimize additional temperature rise.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.

ML433PYA High Reliability Power Inductors

L vs Current



CRITICAL PRODUCTS & SERVICES

1102 Silver Lake Road
Cary, IL 60013
Phone 800-981-0363


Fax 847-639-1508
Email cps@coilcraft.com
www.coilcraft-cps.com

Document ML806-2 Revised 02/06/23




This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

ML433PYA High Reliability Power Inductors


ESR vs Frequency



L vs Frequency



*Height dimension shown is for the mounted part after reflow. Dimension before mounting can be an additional 0.008 inch / 0.2 mm.



Suggested Land Pattern

Dimensions are in $\frac{\text{inches}}{\text{mm}}$



CRITICAL PRODUCTS & SERVICES

© Coilcraft, Inc. 2023

1102 Silver Lake Road
Cary, IL 60013
Phone 800-981-0363

Fax 847-639-1508
Email cps@coilcraft.com
www.coilcraft-cps.com

Document ML806-3 Revised 02/06/23

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.