
Data Line Filters for Critical Applications



Part number ¹	Lines	Current max ² (mA)	Inductance min ³ (µH)	DCR max (mOhms)
ST515FRD5314LZ	4	100	5	250
ST515FRD5354LZ	4	500	5	200
ST515FRD5313LZ	3	100	5	250
ST515FRD5353LZ	3	500	5	200
ST515FRD5312LZ	2	100	5	250
ST515FRD5352LZ	2	500	5	200

1. When ordering, please specify **termination** code:

ST515FRD5352LZ

Termination: L = RoHS compliant tin-silver-copper over tin over nickel over phos bronze.

Special order: **S** = non-RoHS tin-lead (63/37).

- 2. Current rating is for each line.
- 3. Inductance is per winding, tested at 1 MHz.
- 4. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

- Available in 4, 3 and 2-line versions
- Exceptional common mode noise attenuation from 15 MHz to 300 MHz; passes signal line data below 300 MHz with minimal attenuation
- DC current capacity of 500 or 100 mA.
- Excellent electrical isolation (300 Vrms)

Core material Ferrite

Terminations RoHS compliant tin-silver-copper over tin over nickel over phos bronze. Other terminations available at additional cost.

Weight 183 – 201 mg

Ambient temperature -40°C to +85°C


Storage temperature Component: -55°C to +85°C. Tape and reel packaging: -40°C to +80°

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 500/7"reel Plastic tape: 16 mm wide, 0.35 mm thick, 8 mm pocket spacing, 4.4 mm pocket depth


Typical Response*




*Measured on HP 8753D network analyzer. Ref: 50 Ohms.

Document ST925-1 04/16/20

Data Line Filters for Critical Applications





Dimensions are in inches

Document ST925-2 04/16/20