# Outgassing Compliant Air Core Inductors AE426RAT AE446RAT



- Only 2 mm tall
- High Q over a wide range of frequencies
- Low DCR and excellent current handling capability
- High temperature materials allow operation in ambient temperatures up to 155°C.
- Passes NASA low outgassing specifications
- Tin-lead (Sn-Pb) terminations ensure the best possible board adhesion

Part number <sup>1</sup>	Turns	Inductance <sup>2</sup> (nH)	Percent tolerance	Q min³	SRF min <sup>4</sup> (GHz)	DCR max <sup>5</sup> (mOhm)	Imax (A)	Wt (mg)
AE426RAT5N5_SZ	3	5.5	5,2	115	5.0	2.6	4.0	60
AE426RAT9N0_SZ	4	9.0	5,2	120	4.0	3.4	4.0	75
AE426RAT13N_SZ	5	13.0	5,2	100	3.0	3.9	4.0	90
AE446RAT16N_SZ	7	16.0	5,2	110	3.0	5.2	4.0	127
AE446RAT18N_SZ	8	18.0	5,2	110	2.9	6.0	4.0	136
AE446RAT23N_SZ	9	23.0	5,2	110	2.6	6.8	4.0	153
AE446RAT27N_SZ	10	27.0	5,2	110	2.3	7.9	4.0	169

1. When ordering, specify tolerance and screening codes:

#### AE446RAT27NGSZ

Tolerance: G = 2% J = 5%

Screening:

Z = Unscreened

H = Coilcraft CP-SA-10001 Group A

2 = EEE-INST-002 (Family 3) Level 2

3 = EEE-INST-002 (Family 3) Level 3

4 = MIL-STD-981 (Family 50) Class B 5 = MIL-STD-981 (Family 50) Class S

**F** = ESCC3201 (F4 operational life performed at 90°C)

- · Screening performed to the document's latest revision.
- Screening not available for parts with 2% tolerance.
- · Lot qualification (Group B) available.
- Testing T and U have been replaced with more detailed codes 4, 5, and 1, 2, 3, respectively. Codes T and U can still be used, if necessary. Custom testing also available
- 2. Inductance measured at 250 MHz on an Agilent/HP 4286A or equivalent with a Coilcraft SMD-A test fixture and correlation.
- 3. Q measured at 250 MHz on an Agilent/HP 4291A or equivalent with a 16193A test fixture or equivalent.
- 4. SRF measured on an Agilent/HP 8753ES or equivalent with a Coilcraft CCF1268 test fixture.
- 5. DCR measured on a Keithley 580 Micro-Ohmmeter or equivalent.
- 6. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Ambient temperature -55°C to +125°C with Imax current

Maximum part temperature +155°C (ambient + temp rise).

Storage temperature Component: -55°C to +155°C.

Tape and reel packaging: -55°C to +80°C

Terminations Tin-lead (63/37) over copper

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Temperature Coefficient of Inductance (TCL) +5 to +70 ppm/°C

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Enhanced crush-resistant packaging 1000 per 7"reel Plastic tape: 2 mm wide, 0.23 mm thick, 8 mm pocket spacing, 2.2 mm pocket depth



1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363


Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com

Document AE404-1 Revised 02/15/23


This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

# AE426RAT/AE446RAT Low Profile Air Core Inductors

### Typical L vs Frequency



## Typical Q vs Frequency













Size	A max	B max	C max	D	E	F max
426	0.155	0.165	0.079	0.135	0.115 ±0.015	0.029
	3,94	4,19	2,01	3,43	2,92 ±0,38	0,74
446	0.270	0.165	0.079	0.135	0.230 ±0.015	0.029
	6,86	4,19	2,01	3,43	$5,84 \pm 0,38$	0,74

#### **Suggested Land Patterns**





Dimensions are in  $\frac{\text{inches}}{\text{mm}}$ 

#### Strip Length