


**NEW!**

# Outgassing Compliant Power Inductors AR512PJB



- High temperature materials allow operation in ambient temperatures up to 155°C.
- Passes NASA low outgassing specifications
- Special construction allows it to pass vibration testing to 30 G and shock testing to 100 G.
- Tin-lead (Sn-Pb) termination for the best possible board adhesion

**Core material** Ferrite

**Terminations** Tin-lead (63/37) over tin over nickel.

**Weight** 390 – 544 mg

**Ambient temperature** –55°C to +105°C with Irms current

**Maximum part temperature** +155°C (ambient + temp rise)

**Storage temperature** Component: –55°C to +155°C.

**Packaging:** –55°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles


**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Enhanced crush-resistant packaging** 350/7" reel


Plastic tape: 12 mm wide, 0.3 mm thick, 8 mm pocket spacing, 3.68 mm pocket depth

**Recommended pick and place nozzle** OD: 6.2 mm; ID: ≤ 3.1 mm

## Typical L vs Current



## Typical L vs Frequency



**Coilcraft CPS**

CRITICAL PRODUCTS & SERVICES

© Coilcraft, Inc. 2024

1102 Silver Lake Road  
Cary, IL 60013  
Phone 800-981-0363

Fax 847-639-1508  
Email [cps@coilcraft.com](mailto:cps@coilcraft.com)  
[www.coilcraft-cps.com](http://www.coilcraft-cps.com)

Document AR587-1 Revised 05/13/24

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

## AR512PJB Series (6235)




Part number <sup>1</sup>	Inductance <sup>2</sup> ±20% (µH)	DCR <sup>3</sup> max (Ohms)	SRF (MHz) <sup>4</sup>		Isat (A) <sup>5</sup>			Irms (A) <sup>6</sup>	
			min	typ	10% drop	20% drop	30% drop	20°C rise	40°C rise
AR512PJB682MSZ	6.8	0.075	39	55	2.6	2.7	2.8	1.0	1.5
AR512PJB822MSZ	8.2	0.095	34	48	2.5	2.6	2.7	1.0	1.5
AR512PJB103MSZ	10.0	0.100	26	37	2.3	2.4	2.5	1.0	1.4
AR512PJB123MSZ	12.0	0.110	20	29	1.9	2.2	2.3	1.0	1.4
AR512PJB153MSZ	15.0	0.125	18	25	1.9	2.0	2.0	0.97	1.4
AR512PJB183MSZ	18.0	0.140	17	24	1.7	1.8	1.9	0.96	1.3
AR512PJB223MSZ	22.0	0.145	17	24	1.6	1.7	1.7	0.88	1.3
AR512PJB333MSZ	33.0	0.180	11	16	1.3	1.4	1.5	0.80	1.0
AR512PJB473MSZ	47.0	0.245	9.0	13	1.1	1.2	1.2	0.64	0.92
AR512PJB563MSZ	56.0	0.280	8.4	12	1.0	1.0	1.1	0.60	0.86
AR512PJB683MSZ	68.0	0.345	7.6	10.8	0.90	0.94	0.96	0.58	0.80
AR512PJB823MSZ	82.0	0.315	7.0	10.0	0.46	0.52	0.55	0.58	0.76
AR512PJB104MSZ	100.0	0.375	6.3	9.0	0.46	0.52	0.54	0.56	0.72
AR512PJB124MSZ	120.0	0.435	5.8	8.3	0.44	0.48	0.51	0.48	0.64
AR512PJB154MSZ	150.0	0.535	5.1	7.3	0.37	0.43	0.45	0.42	0.58
AR512PJB224MSZ	220.0	0.720	4.0	5.6	0.31	0.36	0.37	0.36	0.51
AR512PJB334MSZ	330.0	1.02	3.0	4.4	0.26	0.29	0.30	0.32	0.44
AR512PJB474MSZ	470.0	1.58	2.5	3.6	0.22	0.25	0.26	0.29	0.40
AR512PJB564MSZ	560.0	1.75	2.2	3.1	0.20	0.22	0.23	0.26	0.37
AR512PJB684MSZ	680.0	1.97	2.0	2.8	0.17	0.19	0.21	0.22	0.32
AR512PJB824MSZ	820.0	2.70	1.8	2.5	0.16	0.18	0.19	0.21	0.26
AR512PJB105MSZ	1000.0	3.20	1.5	2.2	0.14	0.17	0.18	0.19	0.24
AR512PJB155MSZ	1500.0	4.60	1.3	1.9	0.12	0.13	0.14	0.15	0.21
AR512PJB185MSZ	1800.0	5.42	1.2	1.7	0.11	0.12	0.13	0.14	0.18
AR512PJB225MSZ	2200.0	6.40	1.0	1.5	0.090	0.11	0.11	0.13	0.18
AR512PJB335MSZ	3300.0	8.90	0.8	1.1	0.080	0.090	0.10	0.11	0.14
AR512PJB475MSZ	4700.0	14.0	0.66	0.94	0.070	0.077	0.084	0.095	0.12
AR512PJB565MSZ	5600.0	16.4	0.6	0.86	0.070	0.080	0.085	0.080	0.10
AR512PJB685MSZ	6800.0	21.4	0.56	0.80	0.070	0.075	0.080	0.070	0.095
AR512PJB825MSZ	8200.0	24.0	0.49	0.70	0.062	0.070	0.078	0.065	0.090
AR512PJB106MSZ	10000.0	29.0	0.43	0.61	0.059	0.067	0.074	0.060	0.075

1. When ordering, please specify **screening** code:

## AR512PJB106MSZ

- Screening:** Z = Unscreened  
Y = Unscreened (SLDC Option A)  
W = Unscreened (SLDC Option B)  
H = Coilcraft CP-SA-10001 Group A  
G = Coilcraft CP-SA-10001 Group A (SLDC Option A)  
D = Coilcraft CP-SA-10001 Group A (SLDC Option B)  
1 = EEE-INST-002 (Family 1) Level 1  
2 = EEE-INST-002 (Family 1) Level 2  
3 = EEE-INST-002 (Family 1) Level 3  
4 = MIL-STD-981 (Family 04) Class B  
5 = MIL-STD-981 (Family 04) Class S  
F = ESCC3201 (F4 operational life performed at 105°C)
- Screening performed to the document's latest revision.
  - Lot qualification (Group B) available.
  - Testing T and U have been replaced with more detailed codes 4, 5, and 1, 2, 3, respectively. Codes T and U can still be used, if necessary. Custom testing also available.
  - Country of origin restrictions available; prefix options G or F.

- Inductance tested at 100 kHz, 0.1 Vrms using an Agilent/HP 4192A.
  - DCR measured on a micro-ohmmeter.
  - SRF measured using an Agilent/HP 8753ES or equivalent.
  - DC current at 25°C that causes the specified inductance drop from its value without current.
  - Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
  - Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



\* Dimensions are of the case not including the termination. For maximum overall dimensions including the termination, add 0.010 inches / 0,254 mm.

† For optional tin-lead and tin-silver copper terminations, height dimension is after mounting. For maximum height dimension before mounting, add 0.006 inches / 0,152 mm.

Dimensions are in  $\frac{\text{inches}}{\text{mm}}$

**Coilcraft CPS**  
**CRITICAL PRODUCTS & SERVICES**

1102 Silver Lake Road  
Cary, IL 60013  
Phone 800-981-0363

Fax 847-639-1508  
Email cps@coilcraft.com  
www.coilcraft-cps.com

Document AR587-2 Revised 05/13/24

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.