

Outgassing Compliant Chip Inductors AR413RAD

This robust version of Coilcraft's standard 1008HQ series features high temperature materials that pass NASA low outgassing specifications and allow operation in an ambient temperature range of -55°C to 155°C . The standard

tin-lead (Sn-Pb) terminations over leach-resistant base metalization ensures the best possible board adhesion.

All parts are compliant with MIL-STD-981 Family 50, Class S.

Part number ¹	Inductance ³ (nH)	Percent tolerance	Q min ⁴	SRF min ⁵ (GHz)	DCR max ⁶ (mOhms)	I _{max} (A)
AR413RAD3N0_PZ ²	3.0 @ 50 MHz	5	57 @ 1000 MHz	>5.00	38	1.8
AR413RAD4N1_PZ	4.1 @ 50 MHz	5	75 @ 1000 MHz	>5.00	50	1.8
AR413RAD7N8_PZ ²	7.8 @ 50 MHz	5	51 @ 500 MHz	3.80	50	1.6
AR413RAD10N_PZ	10 @ 50 MHz	5,2	60 @ 500 MHz	3.20	60	1.5
AR413RAD12N_PZ	12 @ 50 MHz	5,2	57 @ 500 MHz	2.40	60	1.5
AR413RAD18N_PZ	18 @ 50 MHz	5,2	62 @ 350 MHz	2.10	70	1.4
AR413RAD22N_PZ	22 @ 50 MHz	5,2	62 @ 350 MHz	2.05	70	1.4
AR413RAD33N_PZ	33 @ 50 MHz	5,2	49 @ 150 MHz	1.70	90	1.2
AR413RAD36N_PZ	36 @ 50 MHz	5,2	57 @ 150 MHz	1.40	90	1.1
AR413RAD39N_PZ	39 @ 50 MHz	5,2	45 @ 150 MHz	1.30	90	1.1
AR413RAD47N_PZ	47 @ 50 MHz	5,2,1	45 @ 150 MHz	1.45	120	0.95
AR413RAD56N_PZ	56 @ 50 MHz	5,2,1	43 @ 150 MHz	1.08	120	0.95
AR413RAD68N_PZ	68 @ 50 MHz	5,2,1	54 @ 150 MHz	1.15	130	0.85
AR413RAD82N_PZ	82 @ 50 MHz	5,2,1	54 @ 150 MHz	1.06	160	0.80
AR413RADR10_PZ	100 @ 50 MHz	5,2,1	51 @ 150 MHz	0.82	160	0.80

1. When ordering, please specify **tolerance, termination** and **screening** codes:

AR413RADR10JPZ

Tolerance: F = 1% G = 2% J = 5%

Termination: P = Tin-lead (63/37) over tin over nickel over silver-platinum-glass frit.

S = Tin-lead (63/37) over leach-resistant silver-platinum-glass frit.

L = Silver-palladium-platinum-glass frit

Screening: Z = Unscreened

H = Coilcraft CP-SA-10001 Group A

1 = EEE-INST-002 (Family 3) Level 1

2 = EEE-INST-002 (Family 3) Level 2

3 = EEE-INST-002 (Family 3) Level 3

4 = MIL-STD-981 (Family 50) Class B

5 = MIL-STD-981 (Family 50) Class S

F = ESCC3201 (F4 operational life performed at 90°C)

- Screening performed to the document's latest revision.

- Lot qualification (Group B) available.

- Custom testing also available.

- Country of origin restrictions available; prefix option G or F.

2. Part is wound on low profile coilform.

3. Inductance measured using a Coilcraft SMD-A fixture in an Agilent/HP 4286A impedance analyzer or equivalent with Coilcraft-provided correlation pieces.

4. Q measured using an Agilent/HP 4291A with an Agilent/HP 16197A test fixture or equivalents.

5. SRF measured using an Agilent/HP 8753ES network analyzer or equivalent and a Coilcraft CCF1502 test fixture.

6. DCR measured on a Keithley 580 micro-ohmmeter or equivalent and a Coilcraft CCF858 test fixture.

7. Electrical specifications at 25°C .

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Core material Ceramic

Terminations Tin-lead (63/37) over tin over nickel over silver-platinum-glass frit. Other terminations are also available.

Ambient temperature -55°C to $+125^{\circ}\text{C}$ with I_{max} current

Maximum part temperature $+155^{\circ}\text{C}$ (ambient + temp rise).

Storage temperature Component: -55°C to $+155^{\circ}\text{C}$.

Tape and reel packaging: -55°C to $+80^{\circ}\text{C}$

Resistance to soldering heat Max three 40 second reflows at $+260^{\circ}\text{C}$, parts cooled to room temperature between cycles

Temperature Coefficient of Inductance (TCL) $+25$ to $+155$ ppm/ $^{\circ}\text{C}$

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at $<30^{\circ}\text{C}$ / 85% relative humidity)

Enhanced crush-resistant packaging 2000/7" reel

Standard height parts: Plastic tape: 8 mm wide, 0.23 mm thick, 4 mm pocket spacing, 1.8 mm pocket depth

Low profile parts: Plastic tape: 8 mm wide, 0.3 mm thick, 4 mm pocket spacing, 1.6 mm pocket depth

COILCRAFT ACCURATE
PRECISION REPEATABLE
MEASUREMENTS
SEE WEB SITE **TEST FIXTURES**

Document AR190-1 Revised 08/31/22



CRITICAL PRODUCTS & SERVICES

© Coilcraft, Inc. 2022


1102 Silver Lake Road
Cary, IL 60013
Phone 800-981-0363

Fax 847-639-1508
Email cps@coilcraft.com
www.coilcraft-cps.com



This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

AR413RAD Series (1008)

Typical Q vs Frequency



Typical L vs Frequency



A	B	C	D	E	F	G	H	I	J
max	max	max*	ref						
0.115	0.110	0.080	0.020	0.080	0.020	0.060	0.100	0.040	0.050
2,92	2,79	2,03	0,51	2,03	0,51	1,52	2,54	1,02	1,27

*Low profile parts: 0.050/1,27

Note: Dimensions are before solder application. For maximum overall dimensions including solder, add 0.0025 in / 0,064 mm to **B** and 0.006 in / 0,15 mm to **A** and **C**.