

High-Reliability Power Inductors MS612PNB



- High current, low DCR shielded power inductors
- High temperature materials allow operation in ambient temperatures up to 155°C.
- Tin-lead (Sn-Pb) terminations for the best possible board adhesion

Core material Ferrite

Terminations Tin-lead (63/37) over tin over nickel over phos bronze.

Weight: 3.8 g – 4.6 g

Ambient temperature –55°C to +105°C with Irms current

Maximum part temperature +155°C (ambient + temp rise).

Storage temperature Component: –65°C to +155°C.

Tape and reel packaging: –55°C to +80°C


Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)


Enhanced crush-resistant packaging 500/13" reel;

Plastic tape: 24 mm wide, 0.4 mm thick, 16 mm pocket spacing, 8.1 mm pocket depth

Typical L vs Frequency



Typical L vs Current



MS612PNB Series

Part number ¹	Inductance ² (μ H)	DCR ³ (mOhms)		SRF ⁴ (MHz)		Isat (A) ⁵			Irms (A) ⁶	
		typ	max	min	typ	10% drop	20% drop	30% drop	20°C rise	40°C rise
MS612PNB102NSZ	1.0 \pm 30%	6.3	7.0	80	115	31.84	35.04	36.84	7.1	10.1
MS612PNB142NSZ	1.4 \pm 30%	8.8	9.8	60	85	25.04	27.76	29.52	6.8	9.8
MS612PNB222NSZ	2.2 \pm 30%	9.4	10.5	42	60	22.56	24.80	25.96	6.3	9.2
MS612PNB272NSZ	2.7 \pm 30%	10.1	11.3	28	40	18.76	20.72	22.04	6.1	8.6
MS612PNB392NSZ	3.9 \pm 30%	11.7	13.0	25	35	16.52	18.24	19.20	5.7	7.7
MS612PNB472MSZ	4.7 \pm 20%	13.9	15.5	23	33	15.30	16.90	17.76	4.3	6.2
MS612PNB562MSZ	5.6 \pm 20%	15.7	17.5	21	30	13.38	14.86	15.74	4.3	6.2
MS612PNB682MSZ	6.8 \pm 20%	19.1	21.3	16	23	12.10	13.56	14.20	4.2	6.0
MS612PNB822MSZ	8.2 \pm 20%	20.3	22.6	14	20	11.38	12.60	13.28	4.1	5.9
MS612PNB103MSZ	10 \pm 20%	21.8	24.3	12	17	10.62	11.82	12.48	4.0	5.7
MS612PNB123MSZ	12 \pm 20%	23.2	25.8	11	15	8.90	9.88	10.44	3.7	5.2
MS612PNB153MSZ	15 \pm 20%	27.9	31.0	9.0	13	8.36	9.32	9.94	3.5	4.9
MS612PNB183MSZ	18 \pm 20%	30.8	34.3	8.4	12	8.00	8.88	9.36	3.0	4.5
MS612PNB223MSZ	22 \pm 20%	35.5	39.5	7.7	11	7.08	7.88	8.34	2.9	4.0
MS612PNB273MSZ	27 \pm 20%	45.0	50.0	7.0	10	6.32	7.08	7.54	2.6	3.6
MS612PNB333MSZ	33 \pm 20%	61.9	68.8	6.6	9.5	5.96	6.56	6.98	2.3	3.1
MS612PNB393MSZ	39 \pm 20%	69.1	76.8	6.0	8.5	5.38	5.94	6.28	2.1	3.0
MS612PNB473MSZ	47 \pm 20%	72.3	80.4	5.3	7.5	4.76	5.40	5.66	2.0	2.9
MS612PNB563MSZ	56 \pm 20%	80.2	89.2	4.9	7.0	4.40	4.98	5.30	1.9	2.7
MS612PNB683MSZ	68 \pm 20%	91.3	101.5	4.6	6.5	3.92	4.46	4.74	1.8	2.6
MS612PNB823MSZ	82 \pm 20%	125.9	139.9	3.5	5.0	3.66	4.08	4.38	1.6	2.3
MS612PNB104MSZ	100 \pm 20%	135.1	150.2	3.1	4.5	3.12	3.56	3.78	1.5	2.2
MS612PNB124KSZ	120 \pm 10%	182.3	202.6	3.0	4.3	3.02	3.36	3.58	1.4	1.9
MS612PNB154KSZ	150 \pm 10%	216.5	240.6	2.9	4.1	2.60	2.94	3.10	1.3	1.8
MS612PNB184KSZ	180 \pm 10%	229.0	254.5	2.8	4.0	2.36	2.68	2.84	1.2	1.7
MS612PNB224KSZ	220 \pm 10%	323.6	359.6	2.4	3.4	2.24	2.50	2.62	1.0	1.6
MS612PNB274KSZ	270 \pm 10%	415.6	461.8	2.2	3.1	1.94	2.18	2.34	0.90	1.2
MS612PNB334KSZ	330 \pm 10%	487.3	541.5	2.0	2.9	1.72	1.92	2.06	0.80	1.0
MS612PNB394KSZ	390 \pm 10%	533.6	592.9	1.9	2.7	1.62	1.82	1.92	0.75	1.0
MS612PNB474KSZ	470 \pm 10%	707.5	786.2	1.6	2.2	1.44	1.64	1.74	0.66	0.90
MS612PNB564KSZ	560 \pm 10%	777.4	863.8	1.4	2.0	1.40	1.54	1.66	0.60	0.80
MS612PNB684KSZ	680 \pm 10%	1045	1162	1.2	1.7	1.24	1.32	1.46	0.55	0.75
MS612PNB824KSZ	820 \pm 10%	1166	1296	1.0	1.4	1.14	1.28	1.42	0.50	0.70
MS612PNB105KSZ	1000 \pm 10%	1334	1482	0.90	1.3	0.982	1.08	1.18	0.48	0.68

1. When ordering, please specify **screening** code:

MS612PNB105KSZ

Screening: Z = Unscreened

H = Coilcraft CP-SA-10001 Group A

G = Coilcraft CP-SA-10001 Group A (SLDC Option A)

D = Coilcraft CP-SA-10001 Group A (SLDC Option B)

1/2/3 = EEE-INST-002 (Family 1) Level 1/2/3

4/5 = MIL-STD-981 (Family 04) Class B=4, Class S=5

F = ESCC3201 (F4 operational life performed at 105°C)

- Screening performed to the document's latest revision.
- Lot qualification (Group B) available.
- Testing T and U have been replaced with more detailed codes 4, 5, and 1, 2, 3, respectively. Codes T and U can still be used, if necessary. Custom testing also available.
- Country of origin restrictions available; prefix options G or F.

2. Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc using an Agilent/HP 4263B LCR meter or equivalent.

3. DCR measured on a micro-ohmmeter and a Coilcraft CCF858 test fixture.


4. SRF measured using an Agilent/HP 8753D network analyzer.

5. DC current at 25°C that causes the specified inductance drop from its value without current.

6. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.

7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



* Height dimension is after mounting. For maximum height dimension before mounting, add 0.006 in / 0.152 mm.

Coilcraft CPS
CRITICAL PRODUCTS & SERVICES

1102 Silver Lake Road
Cary, IL 60013
Phone 800-981-0363

Fax 847-639-1508
Email cps@coilcraft.com
www.coilcraft-cps.com

Document MS598-2 Revised 08/22/2022

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.