
High Reliability Power Inductors ML619PYA



- High temperature materials allow operation in ambient temperatures up to 155°C
- High current and very low DCR
- Soft saturation makes them ideal for VRM/VRD applications.

Core material Composite

Terminations Tin-silver over copper.

Weight 9.5 - 11.7 g

Ambient temperature -55°C to $+105^{\circ}\text{C}$ with Irms current.

Maximum part temperature +155°C (ambient + temp rise).

Storage temperature Component: -55°C to +155°C. Tape and reel packaging: -55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Enhanced crush-resistant packaging 300/13" reel Plastic tape: 32 mm wide, 0.3 mm thick, 24 mm pocket spacing, 8.26 mm pocket depth

	Inductance ²	DCR (mOhms)3		SRF (MHz)4		Isat⁵	Irms(A) ⁶	
Part number ¹	±20% (μH)	typ	max	min	typ	(A)	20°C rise	40°C rise
ML619PYA401MLZ	0.40	0.50	0.70	42.4	53.0	111	35.3	45.0
ML619PYA741MLZ	0.74	0.72	0.86	28.1	35.1	86.0	32.4	44.8
ML619PYA102MLZ	1.0	0.93	1.12	24.0	30.0	73.5	30.5	43.1
ML619PYA132MLZ	1.3	1.15	1.38	21.0	26.2	65.0	26.0	35.0
ML619PYA182MLZ	1.8	1.61	1.93	17.0	21.3	57.0	24.9	32.9
ML619PYA202MLZ	2.0	1.91	2.29	16.1	20.1	51.0	22.1	29.9
ML619PYA302MLZ	3.0	2.62	3.10	12.8	16.0	43.0	19.2	25.8
ML619PYA452MLZ	4.5	3.82	4.58	10.0	12.5	34.2	15.3	20.3
ML619PYA532MLZ	5.3	4.35	5.22	9.4	11.8	33.0	14.6	19.9
ML619PYA612MLZ	6.1	5.66	6.79	9.4	11.7	31.0	12.7	17.0

1. When ordering, please specify **screening** code:

ML619PYA612MLZ

Screening: Z = Unscreened

Y = Unscreened (SLDC Option A)

 $\mathbf{W} = \mathsf{Unscreened}$ (SLDC Option B)

H = Group A screening per Coilcraft CP-SA-10001

G = Coilcraft CP-SA-10001 Group A (SLDC Option A)

D = Coilcraft CP-SA-10001 Group A (SLDC Option B)

All screening performed to the document's latest revision

Custom screening also available

- 2. Inductance tested at 100 kHz, 0.1 Vrms using an Agilent/HP 4192A.
- ${\it 3. DCR measured using a micro-ohmmeter.}\\$
- 4. SRF measured using an Agilent/HP 4395A or equivalent.
- 5. DC current at 25°C that causes an inductance drop of 30% (typ) from its value without current.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
- 7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Irms Testing


Irms testing was performed on a 0.060" thick pcb with 4 oz. copper traces optimized to minimize additional temperature rise.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.




ML619PYA Series (1580)


L vs Current





ML619PYA Series (1580)

Typical L vs Frequency









<u> </u>					
	0.520				
	13,2				
0.125 3,18 →					
Suggested					

Part number	Height* max (in / mm)
S19PYA401	0.323 / 8.2
619PYA741	0.323 / 8.2
619PYA102	0.323 / 8.2
619PYA132	0.315 / 8.0
619PYA182	0.315 / 8.0
619PYA202	0.315 / 8.0
619PYA302	0.315 / 8.0
619PYA452	0.315 / 8.0
319PYA532	0.315 / 8.0
319PYA612	0.315 / 8.0

Dimensions are in inches

Land Pattern

* Height dimension shown is for the mounted part after reflow. Dimension before mounting can be an additional 0.008 inch / 0,2 mm.

© Coilcraft, Inc. 2023