
# High-Reliability Power Inductors ML515PMD



- Designed for high-speed switch mode applications
- Can be used as 1:1 transformers or in SEPIC applications

Core material Ferrite

**Terminations** Matte tin over nickel over copper.

**Weight** 0.44 - 0.47 g

Ambient temperature -55°C to +125°C with Irms current

Maximum part temperature +155°C (ambient + temp rise).

Storage temperature Component: -55°C to +155°C.

Tape and reel packaging: -40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at  $<30^{\circ}C$  / 85% relative humidity)

Packaging 500/7" reel; Plastic tape: 16 mm wide, 0.33 mm thick, 12 mm pocket spacing, 3.12 mm pocket depth

### **Single Conductor**

Part number <sup>1,7</sup>	L±20% <sup>2</sup> (µH)	DCR ±5%³ (mOhms)	SRF ref <sup>4</sup> (GHz)	Isat⁵ (A)		
ML515PMM500MLZ	0.050	0.123	3.80	50	40	
ML515PMM640MLZ	0.064	0.123	3.65	32	40	
ML515PMM820MLZ	0.082	0.123	3.75	22	40	
ML515PMM101MLZ	0.100	0.123	3.75	20	40	

#### **Dual Conductor** Leads connected in parallel

### Leads connected in series

Part number <sup>1</sup>	L±20% <sup>2</sup> (μΗ)	DCR ±5% <sup>3</sup> (mOhms)	SRF ref <sup>4</sup> (GHz)	Isat⁵ (A)	Irms <sup>6</sup> (A)	L±20% <sup>2</sup> (μΗ)	DCR max <sup>3</sup> (mOhms)	SRF ref <sup>4</sup> (GHz)	Isat⁵ (A)	Irms <sup>6</sup> (A)
ML515PMD500MLZ	0.050	0.209	3.75	50	38	0.188	1.00	1.50	21	17
ML515PMD640MLZ	0.064	0.209	3.65	32	38	0.272	1.00	1.30	14	17
ML515PMD820MLZ	0.082	0.209	3.75	22	38	0.350	1.00	1.20	11	17
ML515PMD101MLZ	0.100	0.209	3.75	20	38	0.400	1.00	0.950	8	17

When ordering, specify conductors and screening codes:

#### ML515PMD101MLZ

Conductors: M = Single conductor; D = dual conductor

Screening: Z = Unscreened

Y = Unscreened (SLDC Option A)

W = Unscreened (SLDC Option B)

H = Group A screening per Coilcraft CP-SA-10001

G = Coilcraft CP-SA-10001 Group A (SLDC Option A)

**D** = Coilcraft CP-SA-10001 Group A (SLDC Option B)

1/2/3 = EEE-INST-002 (Family 1) Level 1/2/3 4/5= MIL-STD-981 (Family 04) Class B=4, Class S=5

F= Screening per ESCC 3201

- · Screening performed to the document's latest revision.
- Lot qualification (Group B) available.
- · Custom testing also available.
- 2. Inductance tested at 100 kHz, 0.1 Vrms using an Agilent/HP 4263B LCR meter or equivalent.

3. DCR is measured on a micro-ohmmeter at points indicated in the diagram.



▲ Points used for measuring DCR

- 4. This information is for design purposes only and shall not be tested during screening.
- 5. DC current at 25±C that causes an inductance drops of 20% (typ) from its value without current.
- 6. Current that causes a 40°C rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
- 7. Due to the design of this component, DWV and IR shall not be specified or tested.
- 8. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Document ML366-1 Revised 08/11/23

CRITICAL PRODUCTS & SERVICES

1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363


Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.


# High-Reliability Power Inductors – ML515PMM & PMD

# **Typical L vs Current**

# **Single Conductor**




### **Dual Conductor**




# **Typical L vs Frequency**

# **Single Conductor**



## **Dual Conductor**









# High-Reliability Power Inductors – ML515PMM & PMD


# **Typical Temperature Rise vs Current**




# **Current Derating**



# **Dimensions – Single Conductor**




Note: Dimensions are before optional solder application. For maximum overall dimensions including solder, add 0.0025 in / 0,064 mm to the length, and 0.006 in / 0,15 mm to the height.







### **Dimensions – Dual Conductor**




Note: Dimensions are before optional solder application. For maximum overall dimensions including solder, add 0.0025 in / 0,064 mm to the length, and 0.006 in / 0,15 mm to the height.

Dimensions are in  $\frac{inches}{mm}$ 





 $\begin{array}{c|c}
 & 0.177 \\
\hline
0.106 \\
2,70 \\
\hline
 & 0.311 \\
\hline
 & 0.311 \\
\hline
 & 7,90 \\
\hline
 & Parallel mode$ 



Two conductor mode

Suggested Land Patterns

Document ML366-3 Revised 08/11/23



1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363 Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.