
# High Reliability Power Inductors MS512PYA



- High temperature materials allow operation in ambient temperatures up to 155°C
- Tin-lead (Sn-Pb) termination for the best possible board adhesion
- Passes vibration testing to 80 G and shock testing to 1000 G
- Exceptionally low DCR; soft saturation

Terminations Tin-lead (63/37) over copper. Core material Composite Weight 0.6 – 0.7 g Ambient temperature –55°C to +105°C with Irms current Maximum part temperature +155°C (ambient + temp rise).

**Storage temperature** Component: -55°C to +155°C. Tape and reel packaging: -55°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at  ${<}30^\circ\text{C}\,/\,85\%$  relative humidity)

Enhanced crush-resistant packaging 400/7"reel Plastic tape: 16 mm wide, 0.3 mm thick, 12 mm pocket spacing, 3.12 mm pocket depth

Part number <sup>1</sup>	Inductance <sup>2</sup> ±20% (μH)	DCR (mOhms) <sup>3</sup>		SRF (MHz) <sup>4</sup>			Irms (A) <sup>6</sup>	
		typ	max	min	typ	Isat (A) <sup>5</sup>	20°C rise	40°C rise
MS512PYA181MSZ	0.18	1.59	1.75	113	141	39	18.0	24.0
MS512PYA331MSZ	0.33	2.30	2.53	71	89	30	15.0	18.8
MS512PYA561MSZ	0.56	3.01	3.31	49	61	29	12.0	16.5
MS512PYA102MSZ	1.0	5.62	6.18	40	50	23	9.8	13.5
MS512PYA122MSZ	1.2	6.82	7.50	34	43	22	9.0	12.0
MS512PYA182MSZ	1.8	9.57	10.52	27	34	18.2	7.6	10.5
MS512PYA222MSZ	2.2	12.70	13.97	24	30	15.9	5.3	7.5
MS512PYA332MSZ	3.3	19.92	20.81	21	26	12.2	4.5	6.0

1. When ordering, please specify screening code:

#### MS512PYA332MSZ

#### Screening: Z = Unscreened

**Y** = Unscreened (SLDC Option A)

- W = Unscreened (SLDC Option B)
- H = Group A screening per Coilcraft CP-SA-10001
- G = Coilcraft CP-SA-10001 Group A (SLDC Option A)
- **D** = Coilcraft CP-SA-10001 Group A (SLDC Option B)
- All screening performed to the document's latest revision

Custom screening also available

- 2. Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc.
- 3. DCR measured on a micro-ohmmeter.
- 4. SRF measured using an Agilent/HP 4395A or equivalent.
- 5. DC current at 25°C that causes a 30% (typ) inductance drop from its value without current.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
- 7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



CRITICAL PRODUCTS & SERVICES © Coilcraft, Inc. 2023 1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363 Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com

#### Document MS800-1 Revised 05/02/23

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.


#### Irms Testing

Irms testing was performed on a 0.060" thick pcb with 4 oz. copper traces optimized to minimize additional temperature rise.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.

## **MS512PYA Series**

L vs Current






© Coilcraft, Inc. 2023


1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363 Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com Document MS800-2 Revised 05/02/23

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

### **MS512PYA Series**

### L vs Frequency






0.159

4,04

 $\frac{1}{4} = \frac{0.056}{1,43}$ Recommended

Land Pattern

 $\frac{0.216}{5,50}$ 



 Height dimension shown is for the mounted part after reflow.
Dimension before mounting can be an additional 0.008 inch / 0,2 mm.

Dimensions are in  $\frac{inches}{mm}$ 



© Coilcraft, Inc. 2023

1102 Silver Lake Road Cary, IL 60013 Phone 800-981-0363 Fax 847-639-1508 Email cps@coilcraft.com www.coilcraft-cps.com Document MS800-3 Revised 05/02/23

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.