


Outgassing Compliant Power Inductors AE338PWA



- High temperature materials allow operation in ambient temperatures up to 155°C
- Passes NASA low outgassing specifications
- Very low DCR and excellent current handling.
- Soft saturation makes them ideal for VRM/VRD applications.
- Tin-lead (Sn-Pb) termination for the best possible board adhesion
- Special construction allows it to pass vibration testing to 30 G and shock testing to 500 G.

Weight 22 mg

Terminations Tin-lead (63/37) over tin over nickel over silver.

Ambient temperature -55°C to +105°C with Irms current

Maximum part temperature +155°C (ambient + temp rise)

Storage temperature Component: -55°C to +155°C.

Tape and reel packaging: -55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Enhanced crush-resistant packaging 1000/7" reel

Plastic tape: 8 mm wide, 0.23 mm thick, 4 mm pocket spacing, 1.19 mm pocket depth

Part number ¹	Inductance ² ±20% (µH)	DCR (Ohms) ³		SRF (MHz) ⁴		Isat (A) ⁵			Irms (A) ⁶	
		nom	max	min	typ	10% drop	20% drop	30% drop	20°C rise	40°C rise
AE338PWA201MSZ	0.20	0.024	0.027	286	408	2.80	3.45	3.75	2.2	2.8
AE338PWA331MSZ	0.33	0.031	0.035	175	250	1.90	2.75	3.05	1.9	2.6
AE338PWA501MSZ	0.50	0.040	0.045	153	218	1.80	2.35	2.64	1.7	2.3
AE338PWA681MSZ	0.68	0.057	0.063	106	152	1.55	1.95	2.19	1.5	2.1
AE338PWA821MSZ	0.82	0.068	0.075	93	132	1.25	1.65	1.90	1.3	1.7
AE338PWA102MSZ	1.0	0.081	0.089	82	117	1.20	1.60	1.80	1.1	1.6
AE338PWA152MSZ	1.5	0.105	0.116	56	80	0.950	1.30	1.50	1.0	1.4
AE338PWA222MSZ	2.2	0.156	0.173	53	75	0.940	1.20	1.35	0.96	1.3
AE338PWA332MSZ	3.3	0.207	0.228	39	55	0.700	0.925	1.05	0.79	1.1
AE338PWA472MSZ	4.7	0.336	0.370	28	40	0.580	0.750	0.845	0.74	1.0
AE338PWA682MSZ	6.8	0.421	0.463	23	33	0.450	0.620	0.725	0.64	0.87
AE338PWA822MSZ	8.2	0.457	0.503	21	30	0.440	0.600	0.670	0.55	0.75
AE338PWA103MSZ	10	0.555	0.611	20	28	0.390	0.525	0.610	0.49	0.66

1. When ordering, please specify **screening** code:

AE338PWA103MSZ

Screening: **Z** = Unscreened
Y = Unscreened (SLDC Option A)
W = Unscreened (SLDC Option B)
H = Group A screening per Coilcraft CP-SA-10001
G = Coilcraft CP-SA-10001 Group A (SLDC Option A)
D = Coilcraft CP-SA-10001 Group A (SLDC Option B)
 All screening performed to the document's latest revision
 Custom screening also available

2. Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc.

3. DCR measured on a micro-ohmmeter.

4. SRF measured using Agilent/HP 4395A or equivalent.

5. DC current at which the inductance drops the specified amount from its value without current.


6. Current that causes the specified temperature rise from 25°C ambient.

7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

AE338PWA Series

Typical L vs Current



Typical L vs Frequency

