

# Outgassing Compliant Air Core Inductors AE475RAT



- High Q over a wide range of frequencies
- High temperature materials allow operation in ambient temperatures up to 155°C.
- Passes NASA low outgassing specifications
- Tin-lead (Sn-Pb) terminations ensure the best possible board adhesion

**Terminations** Tin-lead (63/37) over copper

**Weight** 80 – 200 mg

**Ambient temperature** –55°C to +125°C with I<sub>max</sub> current

**Maximum part temperature** +155°C (ambient + temp rise).

**Storage temperature** Component: –55°C to +155°C.

Tape and reel packaging: –55°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Temperature Coefficient of Inductance (TCL)** +5 to +70 ppm/°C

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Enhanced crush-resistant packaging** 500 per 7" reel

Plastic tape: 12 mm wide, 0.3 mm thick, 8 mm pocket spacing, 4.2 mm pocket depth

Part number <sup>1</sup>	Inductance <sup>2</sup> (nH)	Percent tolerance	Q <sup>3</sup> typ	Q <sup>3</sup> min	SRF min <sup>4</sup> (GHz)	DCR max <sup>5</sup> (mOhm)	I <sub>max</sub> (A)
AE475RAT22N_SZ	22	5,2	135	100	3.2	4.2	3.0
AE475RAT27N_SZ	27	5,2	135	100	2.7	4.0	3.5
AE475RAT33N_SZ	33	5,2	130	100	2.5	4.8	3.0
AE475RAT39N_SZ	39	5,2	135	100	1.8	4.4	3.0
AE475RAT47N_SZ	47	5,2	135	100	2.1	5.6	3.0
AE475RAT56N_SZ	56	5,2	125	100	1.5	6.2	3.0
AE475RAT68N_SZ	68	5,2	120	100	1.5	8.2	2.5
AE475RAT82N_SZ	82	5,2	120	100	1.3	9.4	2.5
AE475RATR10_SZ	100	5,2	115	100	1.2	12.3	1.7
AE475RATR12_SZ	120	5,2	125	100	1.1	17.3	1.5
AE475RATR15_SZ	150	5,2	145	100	0.75	33.0	1.2

1. When ordering, specify **tolerance** and **screening** codes:

**AE475RATR15GSZ**

**Tolerance:** G = 2% J = 5%

**Screening:** Z = Unscreened

H = Coilcraft CP-SA-10001 Group A

1 = EEE-INST-002 (Family 3) Level 1

2 = EEE-INST-002 (Family 3) Level 2

3 = EEE-INST-002 (Family 3) Level 3

4 = MIL-STD-981 (Family 50) Class B

5 = MIL-STD-981 (Family 50) Class S

F = ESCC3201 (F4 operational life performed at 90°C)

• Screening performed to the document's latest revision.

• Screening not available for parts with 2% tolerance.

• Lot qualification (Group B) available.

• Testing T and U have been replaced with more detailed codes 4, 5, and 1, 2, 3, respectively. Codes T and U can still be used, if necessary. Custom testing also available.

• Country of origin restrictions available; prefix options G.

2. Inductance measured at 150 MHz on an Agilent/HP 4286A or equivalent with a Coilcraft SMD-A test fixture and correlation.

3. Q measured at 150 MHz on an Agilent/HP 4291A or equivalent with a 16193A test fixture or equivalent.

4. SRF measured on an Agilent/HP 8753ES or equivalent with a Coilcraft CCF1268 test fixture.

5. DCR measured on a Keithley 580 Micro-Ohmmeter or equivalent.

6. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

**Coilcraft CPS**  
CRITICAL PRODUCTS & SERVICES

1102 Silver Lake Road  
Cary, IL 60013  
Phone 800-981-0363


Fax 847-639-1508  
Email cps@coilcraft.com  
www.coilcraft-cps.com

Document AE184-1 Revised 04/30/21

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

# AE475RAT Air Core Inductors

## Typical L vs Frequency



## Typical Q vs Frequency

