# Air Core Inductors for Critical Applications ST426RAT ST446RAT



- Only 2 mm tall
- High Q over a wide range of frequencies
- Low DCR and excellent current handling capability

Terminations Tin-silver over copper. Other terminations available at additional cost.

Ambient temperature -40°C to +125°C with Imax current

Maximum part temperature +140°C (ambient + temp rise)

Storage temperature Component: -40°C to +140°C. Tape and reel packaging: -55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Temperature Coefficient of Inductance (TCL) +5 to +70 ppm/°C

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 1000 per 7"reel Plastic tape: 2 mm wide, 0.23 mm thick, 8 mm pocket spacing, 2.2 mm pocket depth

Part number <sup>1</sup>	Turns	Inductance <sup>2</sup> (nH)	Percent tolerance	Q min <sup>3</sup>	SRF min <sup>4</sup> (GHz)	DCR max⁵ (mOhm)	Imax (A)	Wt (mg)
ST426RAT5N5_LZ	3	5.5	5,2	115	5.0	2.6	4.0	60
ST426RAT9N0_LZ	4	9.0	5,2	120	4.0	3.4	4.0	75
ST426RAT13N_LZ	5	13.0	5,2	100	3.0	3.9	4.0	90
ST446RAT16N_LZ	7	16.0	5,2	110	3.0	5.2	4.0	127
ST446RAT18N_LZ	8	18.0	5,2	110	2.9	6.0	4.0	136
ST446RAT23N_LZ	9	23.0	5,2	110	2.6	6.8	4.0	153
ST446RAT27N_LZ	10	27.0	5,2	110	2.3	7.9	4.0	169

1. When ordering, specify tolerance, terminations and testing codes:

ST446RAT27NGLZ

Tolerance: G = 2% J = 5%

**Termination:** L = Tin-silver over copper.

Special order:

T = Tin-silver-copper (95.5/4/0.5) over copper,

S = Tin-lead (63/37) over copper.

Testing:

H = Group A screening per Coilcraft CP-SA-10001 All screening performed to the document's latest revision

Custom screening also available


- 2. Inductance measured at 250 MHz on an Agilent/HP 4286A or equivalent with a Coilcraft SMD-A test fixture and correlation.
- 3. Q measured at 250 MHz on an Agilent/HP 4291A or equivalent with a 16193A test fixture or equivalent.
- 4. SRF measured on an Agilent/HP 8753ES or equivalent with a Coilcraft CCF1268 test fixture.
- 5. DCR measured on a Keithley 580 Micro-Ohmmeter or equivalent.
- 6. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.




## ST426RAT/ST446RAT Low Profile Air Core Inductors

### Typical L vs Frequency



## Typical Q vs Frequency










<b>├</b> ─ E→
\mmm
F→Ï←

Size	A max	B max	C max	D	E	F max
426	0.155	0.165	0.079	0.135	0.115 ±0.015	0.029
	3,94	4,19	2,01	3,43	2,92 ±0,38	0,74
446	0.270	0.165	0.079	0.135	0.230 ±0.015	0.029
	6,86	4,19	2,01	3,43	$5.84 \pm 0.38$	0,74

#### Strip Length



#### **Suggested Land Patterns**



Dimensions are in  $\frac{\text{inches}}{\text{mm}}$ 

Please check our web site for latest information.

Document ST404-1 Revised 05/03/18