

High-Reliability Power Inductors MS427PJB



- High temperature materials allow operation in ambient temperatures up to 155°C.
- Special construction allows it to pass vibration testing to 80 G and shock testing to 1000 G.
- Tin-lead (Sn-Pb) termination for the best possible board adhesion

Core material Ferrite

Terminations Tin-lead (63/37) over tin over nickel.

Weight 83 – 138 mg

Ambient temperature –55°C to +105°C with Irms current

Maximum part temperature +155°C (ambient + temp rise)

Storage temperature Component: –55°C to +155°C.

Tape and reel packaging: –55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Enhanced crush-resistant packaging 1000/7" reel
Plastic tape: 12 mm wide, 0.3 mm thick, 8 mm pocket spacing, 1.52 mm pocket depth

| Part number ¹ | Inductance ² ±20% (µH) | DCR max ³ (Ohms) | SRF (MHz) ⁴ | | Isat (A) ⁵ | | | Irms (A) ⁶ | |
|--------------------------|--------------------------------------|-----------------------------------|------------------------|------|-----------------------|-------------|-------------|-----------------------|--------------|
| | | | min | typ | 10% drop | 20% drop | 30% drop | 20°C rise | 40°C rise |
| MS427PJB301MSZ | 0.30 | 0.040 | 329 | 470 | 5.6 | 5.7 | 5.8 | 1.9 | 2.6 |
| MS427PJB501MSZ | 0.50 | 0.050 | 231 | 330 | 4.3 | 4.4 | 4.5 | 1.7 | 2.2 |
| MS427PJB801MSZ | 0.80 | 0.055 | 157 | 225 | 3.7 | 3.75 | 3.8 | 1.5 | 2.0 |
| MS427PJB102MSZ | 1.0 | 0.060 | 133 | 190 | 3.0 | 3.1 | 3.2 | 1.4 | 1.8 |
| MS427PJB152MSZ | 1.5 | 0.078 | 105 | 150 | 2.9 | 3.1 | 3.2 | 1.2 | 1.6 |
| MS427PJB182MSZ | 1.8 | 0.087 | 91.0 | 130 | 2.7 | 2.8 | 2.9 | 1.2 | 1.5 |
| MS427PJB222MSZ | 2.2 | 0.110 | 80.0 | 115 | 2.2 | 2.3 | 2.35 | 1.0 | 1.3 |
| MS427PJB332MSZ | 3.3 | 0.165 | 59.0 | 85.0 | 1.8 | 1.9 | 1.95 | 0.92 | 1.2 |
| MS427PJB472MSZ | 4.7 | 0.215 | 47.0 | 68.0 | 1.4 | 1.5 | 1.55 | 0.72 | 1.0 |
| MS427PJB562MSZ | 5.6 | 0.260 | 40.0 | 58.0 | 1.4 | 1.4 | 1.5 | 0.60 | 0.88 |
| MS427PJB682MSZ | 6.8 | 0.270 | 37.0 | 54.0 | 1.2 | 1.3 | 1.4 | 0.56 | 0.80 |
| MS427PJB822MSZ | 8.2 | 0.350 | 35.0 | 50.0 | 1.1 | 1.3 | 1.3 | 0.56 | 0.78 |
| MS427PJB103MSZ | 10 | 0.380 | 30.0 | 43.0 | 1.1 | 1.2 | 1.3 | 0.56 | 0.76 |
| MS427PJB123MSZ | 12 | 0.380 | 26.0 | 38.0 | 0.94 | 0.97 | 1.0 | 0.53 | 0.70 |
| MS427PJB153MSZ | 15 | 0.440 | 25.0 | 36.0 | 0.85 | 0.89 | 0.92 | 0.50 | 0.66 |
| MS427PJB183MSZ | 18 | 0.530 | 21.0 | 31.0 | 0.76 | 0.80 | 0.82 | 0.45 | 0.60 |
| MS427PJB223MSZ | 22 | 0.590 | 19.0 | 27.0 | 0.69 | 0.72 | 0.74 | 0.42 | 0.54 |
| MS427PJB333MSZ | 33 | 0.715 | 16.0 | 23.0 | 0.47 | 0.49 | 0.51 | 0.39 | 0.52 |
| MS427PJB473MSZ | 47 | 0.935 | 12.0 | 18.0 | 0.39 | 0.42 | 0.43 | 0.35 | 0.46 |
| MS427PJB563MSZ | 56 | 1.15 | 11.0 | 16.0 | 0.37 | 0.39 | 0.40 | 0.34 | 0.43 |
| MS427PJB683MSZ | 68 | 1.35 | 10.2 | 14.6 | 0.32 | 0.33 | 0.34 | 0.29 | 0.38 |
| MS427PJB104MSZ | 100 | 1.90 | 7.7 | 11.0 | 0.26 | 0.28 | 0.285 | 0.25 | 0.32 |
| MS427PJB124MSZ | 120 | 2.60 | 7.0 | 10.0 | 0.23 | 0.24 | 0.25 | 0.22 | 0.27 |
| MS427PJB154MSZ | 150 | 3.10 | 6.3 | 9.0 | 0.22 | 0.23 | 0.24 | 0.19 | 0.26 |
| MS427PJB224MSZ | 220 | 4.10 | 4.7 | 6.7 | 0.18 | 0.20 | 0.20 | 0.18 | 0.23 |
| MS427PJB334MSZ | 330 | 6.00 | 3.9 | 5.6 | 0.14 | 0.16 | 0.165 | 0.14 | 0.18 |
| MS427PJB474MSZ | 470 | 9.50 | 3.0 | 4.3 | 0.13 | 0.14 | 0.145 | 0.11 | 0.18 |
| MS427PJB564MSZ | 560 | 10.7 | 2.8 | 4.0 | 0.12 | 0.13 | 0.14 | 0.10 | 0.14 |
| MS427PJB684MSZ | 680 | 11.7 | 2.4 | 3.5 | 0.10 | 0.11 | 0.12 | 0.10 | 0.14 |
| MS427PJB824MSZ | 820 | 15.1 | 2.1 | 3.0 | 0.10 | 0.105 | 0.11 | 0.090 | 0.11 |
| MS427PJB105MSZ | 1000 | 16.3 | 1.8 | 2.6 | 0.10 | 0.102 | 0.106 | 0.080 | 0.10 |
| MS427PJB155MSZ | 1500 | 26.4 | 1.5 | 2.2 | 0.096 | 0.099 | 0.100 | 0.070 | 0.090 |
| MS427PJB185MSZ | 1800 | 35.0 | 1.3 | 1.9 | 0.089 | 0.094 | 0.097 | 0.060 | 0.080 |
| MS427PJB225MSZ | 2200 | 42.5 | 1.3 | 1.9 | 0.082 | 0.089 | 0.092 | 0.050 | 0.070 |
| MS427PJB335MSZ | 3300 | 56.0 | 0.90 | 1.3 | 0.072 | 0.078 | 0.083 | 0.040 | 0.060 |

1. When ordering, please specify screening code:

MS427PJB335MSZ

Screening:

- Z = Unscreened
 - Y = Unscreened (SLDC Option A)
 - W = Unscreened (SLDC Option B)
 - H = Coilcraft CP-SA-10001 Group A
 - G = Coilcraft CP-SA-10001 Group A (SLDC Option A)
 - D = Coilcraft CP-SA-10001 Group A (SLDC Option B)
 - 1/2/3 = IEEE-INST-002 (Family 1) Level 1/2/3
 - 4/5 = MIL-STD-981 (Family 04) Class B=4, Class S=5
 - F = ESCC3201 (F4 operational life performed at 105°C)
- Screening performed to the document's latest revision.
 - Lot qualification (Group B) available.
 - Testing T and U have been replaced with more detailed codes 4, 5, and 1, 2, 3, respectively. Codes T and U can still be used, if necessary. Custom testing also available.
 - Country of origin restrictions available; prefix options G or F.

2. Inductance tested at 100 kHz, 0.1 Vrms using an Agilent/HP 4192A.

3. DCR measured on a micro-ohmmeter.

4. SRF measured using an Agilent/HP 8753ES or equivalent.

5. DC current at 25°C that causes the specified inductance drop from its value without current.

6. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.

7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Document MS548-1 Revised 04/24/23

Coilcraft CPS
CRITICAL PRODUCTS & SERVICES


1102 Silver Lake Road
Cary, IL 60013
Phone 800-981-0363

Fax 847-639-1508
Email cps@coilcraft.com
www.coilcraft-cps.com




This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.

MS427PJB Series (4414)

Typical L vs Current



Typical L vs Frequency



*Dimensions are of the case not including termination. For maximum overall dimensions including the termination, add 0.010 inches / 0,254 mm.

† Height dimension is after mounting. For maximum height dimension before mounting, add 0.006 in / 0,152 mm.

Dimensions are in $\frac{\text{inches}}{\text{mm}}$



CRITICAL PRODUCTS & SERVICES

© Coilcraft, Inc. 2023

1102 Silver Lake Road
Cary, IL 60013
Phone 800-981-0363

Fax 847-639-1508
Email cps@coilcraft.com
www.coilcraft-cps.com

Document MS548-2 Revised 04/24/23

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.